

Lapping and Polishing System

Logitech PM 5

Principle

Lapping and polishing of samples with a very flat surface.

Manufacturer	Logitech
Disc Diameter	300 mm
Rotational Speed Disc	4 - 70 rpm
Polishing Jig PP6GT	Glass substrate, diameter 102 mm
Pressure Force	max. 3.3 kg
Max. Flatness	$\leq 10 \mu\text{m}$ when $l = 4.5 \text{ cm}$
Accessory	Dial gauge for abrasion in height and for measuring sample dimension, thin section bonding jigs, force measurement
